





CLEVER DISPENSE 06

Set H DPH

The CLEVER DISPENSE 06 H is a professional dispenser for applications that require highest accuracy and a maximum control of material viscosity. These dispensers allow heating of the dispensing nozzle and cartridge. The CLEVER DISPENSE 06 H DP Sets are designed for manual dispensing operations.

The all-electronic dispensers whose dispensing pressure, temperature and retract vacuum are program-controlled use the time-pressure-technology. This allows reliable dispensing of very small dots and lines of liquid to pasty material either as 1K-type or 2K-type. In addition, a sensor measures the material temperature inside the dispensing pen and the control unit compensates the material-specific change in viscosity. You can add your own material to the already existing material library to define essential material parameter and limit values.



Manual dispensing with heatable dispensing pen.

A consistent volume can be

dispensed with the volumetric

dispensing device, regardless of the

Intuitive software offering use of

dispensing recipes and the material

Repeatability

viscosity

library

Software



Fully electronic dispensing device Manual procedure

Temperature control Heatable dispensing nozzle for regulating temperature of the medium

Standard equipment

- Control unit CLEVER DISPENSE 06
- Dispensing pen (size of choice) with integrated nozzle heater and connecting cable (1,5m)
- Stand for dispensing pen, foot switch, needle set (27pcs), Pneumatic hose (d=6mm; I=5m)
- Power supply 90-230 V AC -> 24V DC
- PC-Software CLEVER DISPENSE Pro
- USB cable
- Short instruction

Technical details

Cartridges to use:	3, 5, 10, 30, 55 ccm	Line dispense settings:	Time range:	0,1s-30s
Viscosity range:	0.1-10⁵ mPas		Continuous pressure control	
Nozzle heater:	90°C max.		Repeatability:	2% (Pressure level)
Communication:	USB 2 (Typ B) / SPS / PLC / Network	Dot dispense settings:	Time range:	0,001 s -2 s (±0,0005 s
ewicht:	2,5 kg max		Pressure range:	0,1 bar - 6 bar
Größe:	272 x 152 x 60 mm3		Repeatability:	1% (Pressure pulse)
			Smallest dispensing vol.:	1.0 nl

Options

Retract vacuum:

-20 mbar - 0 mbar

throu

Exceptional technical support through evaluation of material properties and application assistance

Dispensing pressure, temperature

and retract vacuum are configured

Process reliability

through the program

Support

CLEVER DISPENSE 06 H DPH: Optional extras

	Article nr.	Name
	Set variati	ons
	CD06.0202	CLEVER DISPENSE 06 H DPH 5
	CD06.0203	CLEVER DISPENSE 06 H DPH 10
	Optional extras	
	CD06.0050	Vacuum module CD06 H
	DK06.1005	Cartridge Heater 30 and 55ccm
<u>+</u> 1	PD80.1011	Dispensing pen 3ccm
<i>+</i> 1	PD80.1012	Dispensing pen 5ccm
<i>#</i> 1	PD80.1013	Dispensing pen10ccm
<i>#</i> 1	PD80.1014	Dispensing pen 30ccm
₽	PD60.1012	Dispensing pen 5ccm with nozzle heating
₽.	PD60.1013	Dispensing pen 10ccm with nozzle heating
]	PD60.1014	Dispensing pen 30ccm with nozzle heating
5	PD10.0012	Stand for dispensing pen for 3 & 5ccm cartridges
5	PD10.0013	Stand for dispensing pen for 10ccm cartridges
5	PD10.0014	Stand for dispensing pen for 30ccm cartridges
	PD91.0003	Foot switch for CD06/SD06

More accessories and consumables at www.martin-smt.de

MARTIN GmbH Industriestrasse 17 82110 Germering / Germany Fon: +49(0)898941898-0 Fax.: +49(0)898941898-19 Web: www.martin-smt.de Es gelten unsere allgem. Lieferbedingungen Technische Änderungen vorbehalten